




L-Series 2.2 - 7.5 kW



The L-Series from CompAir

Well known in the industry for quality and reliability, CompAir continuously develops the L-Series to achieve cutting edge performance and efficiency. The L02-L06 range of lubricated screw compressors comprises of many different models and versions to allow maximum flexibility.



Engineering excellence

Compressors are more than just a financial investment, they are a key component in ensuring that manufacturers, processors and operators receive consistent, high quality low cost air. The screw compression element is the heart of the compressor and therefore CompAir keeps the design and manufacture in-house, using the latest CNC rotor grinding machinery, coupled with online laser technology.

The resulting reliability and performance ensure that operating costs will remain low throughout the compressor's life.



Engineered for total piece of mind

Thanks to the user-friendly design, these compressors are easy to use, easy to install and fully ready for plug and play. Designed with a minimum number of moving parts, the compressors are very reliable, robust and capable to run continuously. The new canopy design of the compressors guarantees a quick and easy maintenance, minimising the downtime and maximising the reliability.







Compact & Flexible

Reliable electric motor IP55, F-class insulation, IE3 class

Cofety devices for

- Safety devices for • Motor over temperature
- Compressor over temperature
- Airend rotation

Receiver mounted

High quality receiver built to EN87/404 (AD2000)

Airstation

Equipped with high performance dryer featuring intelligent control system for low pressure losses.

- Pressure dew point +3°C (ISO 7183, A)
- Environmentally friendly refrigerant R134a
- Digital controller displaying:
 - · Dew point indication
 - Additional energy saving mode
 - · Maintenance display
 - Fault memory

Small footprint

The compressor itself requires a minimum floor space of only 62 x 60 cm, with the receiver mounted models being exceptionally space-saving.

4 - 7.5kW extended features

- Star Delta starter is included as standard from 4 up to 7.5kW
- 5.5 + 7.5 kW variants include an after cooler also as standard to optimise air quality and minimise the size of downstream needed



Maximum flexibility

Based on the individual customer requirements the compressors can be combined with different options to provide everything from a stand alone compressor to the complete airstation.

The options include:



Compressor base mounted



Receiver mounted compressor



Complete airstation including compressor, dryer and receiver



New C-Pro1.0+ User-friendly control system

The new compressor controller C-Pro1.0+ is equipped as standard for all models and provides information about pressure, oil temperature and compressor status (load/unload) together in one display and offers many useful features, such as:

- Communication port RS485 supporting Modbus
- Integrated sequencer for easy control for 2 compressors
- Plastic box for higher IP protection degree
- Auto restart after black-out
- Password protection
- · Air and oil filter replacement
- · Separator filter replacement and oil change
- · Pressure setting easily adjustable
- Unload timer for both DOL & SDS

Optional equipment

- Receivers available at 270lt and 500lt for L04-L06
- Prefilter and microfilter combination
- Timed or float drains for receiver mounted units and airstation

CompAir L-Series - Technical Data

Base Mounted

Compressor Model	Maximum Pressure	FAD @ 10 bar/145 psi ¹⁾	Motor		Starter Options	Receiver Size	Noise Level ²⁾	Weight	Dimensions L x W x H
	[bar g]	[m³/min]	[kW]	[hp]		[0]	[dB(A)]	[kg]	[mm]
L02 - (230 V)	10	0.18	2.2	3	DOL	-	63	151	600 x 650 x 1100
L02	10	0.21	2.2	3	DOL	-	63	151	600 x 650 x 1100
L03	10	0.35	3	4	DOL	-	64	151	600 x 650 x 1100
L04	10	0.45	4	5	Star-Delta	-	67	154	600 x 650 x 1100
L05	10	0.66	5.5	7	Star-Delta	-	68	173	600 x 650 x 1100
L06	10	0.89	7.5	10	Star-Delta	-	70	179	600 x 650 x 1100

Receiver Mounted

Compressor Model	Maximum Pressure	FAD @ 10 bar/145 psi ¹⁾	Motor		Starter Options	Receiver Size	Noise Level ²⁾	Weight	Dimensions L x W x H
	[bar g]	[m³/min]	[kW]	[hp]		[0]	[dB(A)]	[kg]	[mm]
L02- 270 (230V)	10	0.18	2.2	3	DOL	270	63	242	1539 x 720 x 1604
L02- 270	10	0.21	2.2	3	DOL	270	63	242	1539 x 720 x 1604
L03-270	10	0.35	3	4	DOL	270	64	242	1539 x 720 x 1604
L04-270	10	0.45	4	5	Star-Delta	270	67	245	1539 x 720 x 1604
L04-500	10	0.45	4	5	Star-Delta	500	67	314	1885 x 720 x 1700
L05-270	10	0.66	5.5	7	Star-Delta	270	68	263	1539 x 720 x 1604
L05-500	10	0.66	5.5	7	Star-Delta	500	68	333	1885 x 720 x 1700
L06-270	10	0.89	7.5	10	Star-Delta	270	70	269	1539 x 720 x 1604
L06-500	10	0.89	7.5	10	Star-Delta	500	70	339	1885 x 720 x 1700

AIRSTATION³⁾

Compressor Model	Maximum Pressure	FAD @ 10 bar/145 psi 1)	Motor		Starter Options	Receiver Size	Noise Level ²⁾	Weight	Dimensions L x W x H
	[bar g]	[m³/min]	[kW]	[hp]		DI	[dB(A)]	[kg]	[mm]
L02FS- 270 (230V)	10	0.18	2.2	3	DOL	270	63	261	1539 x 720 x 1604
L02FS- 270	10	0.21	2.2	3	DOL	270	63	261	1539 x 720 x 1604
L03FS-270	10	0.35	3	4	DOL	270	64	261	1539 x 720 x 1604
L04FS-270	10	0.45	4	5	Star-Delta	270	67	270	1539 x 720 x 1604
L04FS-500	10	0.45	4	5	Star-Delta	500	67	339	1885 x 720 x 1700
L05FS-270	10	0.66	5.5	7	Star-Delta	270	68	289	1539 x 720 x 1604
L05FS-500	10	0.66	5.5	7	Star-Delta	500	68	358	1885 x 720 x 1700
L06FS-270	10	0.89	7.5	10	Star-Delta	270	70	295	1539 x 720 x 1604
L06FS-500	10	0.89	7.5	10	Star-Delta	500	70	364	1885 x 720 x 1700

 $^{^{1]}}$ Data measured and stated in accordance with ISO 1217 Ed. 4, Annex C and the following conditions: Air Intake Pressure 1 bar a ; Air Intake Temperature 20° C ; Humidity 0 % (dry)







 $^{^{2]}}$ Measured in free field conditions in accordance with ISO 2151, tolerance \pm 3 dB(A)

 $^{^{\}rm 3I}$ The refrigerant dryer requires a separate electric supply. Data refer to ISO 7183, A; pressure dew point 3° C



Global experience truly local service

With over 200 years of engineering excellence, the CompAir brand offers an extensive range of highly reliable, energy efficient compressors and accessories to suit all applications.

An extensive network of dedicated CompAir sales companies and distributors across all continents provide global expertise with a truly local service, ensuring our advanced technology is backed up with the right support.



CompAir compressed air product range

Advanced Compressor Technology Lubricated

- Rotary Screw
 - > Fixed and Regulated Speed
- Piston
- Portable

Oil-Free

- · Water Injected Screw
 - > Fixed and Regulated Speed
- Two Stage Screw
 - > Fixed and Regulated Speed
- Pistor
- · High Speed Centrifugal Quantima®
- Rotary Scroll

Complete Air Treatment Range

- Filter
- · Refrigerant and Desiccant Dryer
- · Condensate Management
- Heat of Compression Dryer
- Nitrogen Generator

Modern Control Systems

- CompAir DELCOS Controllers
- · SmartAir Master Sequencer
- · iConn Smart Flow Management

CompAir policy is one of continuous improvement and we therefore reserve the right to alter specifications and prices without prior notice. All products are sold subject to the Company's conditions of sale.

Value Added Services

- Professional Air Audit
- · Performance Reporting
- · Leak Detection

Leading Customer Support

· Custom Engineered Solutions

PureAir

ULTIMA U160

- · Local Service Centres
- Genuine CompAir Parts and Lubricants