COMPRESSOR DATA SHEET

Gardner Denver

In Accordance with Federal Uniform Test Method for Certain Lubricated Air Compressors

Rotary Compressor: Fixed Speed

MODEL DATA - FOR COMPRESSED AIR

WODEL DATA - FOR COMI REDDED MIR								
1	Manufacturer: Gardner	Denver						
	Model Number: STG2-200hp-125psi		Date:	1/4/2021				
2	X Air-cooled Wat	er-cooled	Type:	Screw				
			# of Stages:	1				
3*	Rated Capacity at Full Load Operat	ing Pressure ^{a, e}	986.0	acfm ^{a,e}				
4*	Full Load Operating Pressure ^b		125	psig ^b				
5	Maximum Full Flow Operating Pressure ^c		125	psig ^c				
6	Drive Motor Nominal Rating		200	hp				
7	Drive Motor Nominal Efficiency		96.2	percent				
8	Fan Motor Nominal Rating (if applicable)		5	hp				
9	Fan Motor Nominal Efficiency		85.5	percent				
10*	Total Package Input Power at Zero	Flow ^e	47.6	kW ^e				
11	Total Package Input Power at Rated Capacity and Full Load Operating Pressure ^d		182.70	kW^d				
12*	Package Specific Power at Rated Capacity and Full Load Operating Pressure ^e		18.53	kW/100 cfm ^e				
13	Isentropic Efficiency		81.07	Percent				

*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator.

Consult CAGI website for a list of participants in the third party verification program: <u>www.cagi.org</u>



Compressed Air & Gas Institute

- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex C; ACFM is actual cubic feet per minute at inlet conditions.
- b. The operating pressure at which the Capacity (Item 3) and Electrical Consumption (Item 11) were measured for this data sheet.
- c. Maximum pressure attainable at full flow, usually the unload pressure setting for load/no load control or the
- maximum pressure attainable before capacity control begins. May require additional power.
- d. Total package input power at other than reported operating points will vary with control strategy.
- e. Tolerance is specified in ISO 1217, Annex C, as shown in table below:

NOTE: The terms "power" and "energy" are synonymous for purposes of this document.

Member	m^3 / min	2			No Load / Zero Flow Power
П Г		<u>ft³ / min</u>	%	%	%
	Below 0.5	Below 17.6	+/- 7	+/- 8	
	0.5 to 1.5	17.6 to 53	+/- 6	+/- 7	+/- 10%
	1.5 to 15	53 to 529.7	+/- 5	+/- 6	+/- 10%
ROT 030.1	Above 15	Above 529.7	+/- 4	+/- 5	
12/19 Rev 3 This form was developed	by the Compressed Air an	d Gas Institute for the use of its members participating in t	he PVP. CAGI has not indepen	idently verified the reported data	

Configurator: ST125-200G2A