
## P2620 Liquid Ring Vacuum Pumps and Compressors




by Gardner Denver

Designed to operate in demanding environments such as paper, power, mining and chemical process industries, this pump combines durability and reliability with low operating costs. The P2620 has a polyisoprene-lined body for corrosion and erosion resistance. This is a standard feature.

The unique inlet configuration allows for both top and side inlet arrangements to accommodate low headroom installations. Bottom and side discharge connections offer flexibilty to address installation space constraints.



For more aggressive applications, stainless steel, stainless steel clad and epoxy coated components are available.



## **Dimensions** mm in blue

 Pump
 A
 B
 C
 D
 E
 Inlet
 Outlet

 P-2620
 169 4293
 80 79 2032
 79 902
 35.5 9.8 16 in. FLG. 400mm FLG. 350mm FLG
 14 in. FLG. 350mm FLG

All dimensions are approximate

Inlet (both ends)