

DRY-BREAK[™] 3-INCH

Emco Wheaton DRY-BREAK™ Couplers and Adapters are used anywhere spill-free fluid transfer is required.

COUPLER



- Cannot be opened until connected to adapter or disconnected until lever is moved to closed position thus eliminating accidental spillage
- Product loss on disconnect virtually eliminated
- Available with straight or 90° integrated ball-bearing swivel for loading arm or kink-free hose connection
- Easily serviced in the field using the Emco Wheaton Repair Kit Program
- Interchangeable with all existing Emco Wheaton 3" inlet adapters





- Enhanced poppet design allows for better flow characteristics in either direction
- Rear-entry design allows for easy field servicing
- One-piece poppet means fewer components for service
- Interchangeable with all existing Emco Wheaton 3" inlet couplers




www.emcowheaton.com

✓ @EmcoWheaton | f www.facebook.com/EmcoWheaton

©2019 Emco Wheaton. All Rights Reserved. All trademarks are the property of Emco Wheaton.

ACCESSORIES





Maximum Working Pressure: 85 psi

TO ORDER 3-INCH PRODUCTS

J73C-AVN1-B003

Туре	Body Material	Seals	Inlet	Swivel	Rev.	Special Features
C=Coupler	A=Aluminum	V=Viton	N=Female NPT	0=Straight (No Swivel)	А	003=Selective (3-pin)
A=Adapter	B=Brass	B=Buna	I=ISO 228 Parallel	1=Straight with Swivel	В	004=Dust Cap
				2=90° with Swivel	etc.	

CRN available for all provinces and territories.

Perfluoroelastomer (Chemraz): -20°F to 450°F (-29°C to 232°C) Buna: -40°F to 225°F (-40°C to 107°C) Viton: 5°F to 225°F (-15°C to 204°C)

www.emcowheaton.com

🔰 @EmcoWheaton | f www.facebook.com/EmcoWheaton

©2019 Emco Wheaton. All Rights Reserved. All trademarks are the property of Emco Wheaton.