



45-70 KW VARIABLE SPEED ROTARY SCREW COMPRESSOR

VS Series™

Constant Efficiency

The VS Series™ from Gardner Denver features the time proven ENDURO®+ air end and ensures that maximum reliability and the highest efficiency levels are incorporated into these compact packages. The VS Series™ utilizes a rotor profile and variable speed drive/motor/compressor combination that results in the lowest specific power over the widest operating range. Choosing a VS Series™ compressor is the right choice when you need constant efficiency.

Smarter Solution

The VS Series™ compressor packages are the smarter solution to your complex air system needs. Using a smart thermal mixing valve, these compressors' mixing valves are electronically controlled on ambient temperature versus a fixed temperature valve that competitors typically use. The single pass cooler design eliminates thermal stress on the oil cooler while the TEAO premium efficiency motors ensure a separate, constant speed fan to cool the motor.

Information at your Fingertips

All VS Series™ compressors come equipped with the AirSmart™ microprocessor controller. VS Series™ compressors use microprocessor control technology because it's the simplest, yet most powerful compressor control design available. The AirSmart™ from Gardner Denver is built on the foundation of being easy to operate and an industry leader in self-diagnostic, protective shutdown, service advisory and full text digital display capabilities.

Gardner
Denver

VS45-70 ROTARY SCREW COMPRESSOR, 60 HZ

MODEL	DRIVE MOTOR		NOMINAL PRESSURE		FAD ¹		NOISE LEVEL ² DB(A)	WEIGHT		DIMENSIONS L x W x H IN. (MM)
	HP	KW	PSIG	BAR	ACFM	M ³ /MIN		LBS	KG	
VS45	60	45	100	6.9	308	8.73	68			
			125	8.6	269	7.62				
			175	12.0	206	5.84				
VS50	67	50	100	6.9	348	9.86	69	3180	1442	85 x 44 x 75 (2159 x 1118 x 1905)
			125	8.6	322	9.12				
			175	12.0	245	6.94				
VS70	94	70	100	6.9	436	12.35	71			
			125	8.6	395	11.19				
			175	12.0	318	9.01				

1) Data measured and stated in accordance with ISO1217, Ed. 4, Annex C & Annex E at the following conditions:

Air Intake Pressure 1 bar A, Air Intake Temperature 20° C, Humidity 0% (Dry)

2) Measured in free field conditions in accordance with ISO 2151, tolerance +/- 3 dB

VS Series™ Features (45-70 kW)

- Direct drive, oil flooded, single stage rotary screw air compressor
- AEON 9000SP lubricant
- AirSmart™ microprocessor controller
- Air-cooled standard
- Allen Bradley inverter drive
- CSA labeled and approved electrical controls and wiring
- cUL labeled electronics (UL 508A)
- EMC filter (standard or optional depending on model and voltage) and DC bus choke
- Integrated air filter
- Integrated spin-on oil filter and air/oil separator
- IP54 electrical enclosure
- Moisture separator
- Optional automatic water temperature regulator
- Optional Communication Module
- Optional integrated dryer
- Optional line reactor (shipped loose)
- Optional water cooling
- Quiet enclosure
- TEAO main motor
- Smart thermostatic mixing valve
- Voltage: 460 / 575V (3 phase only)

Gardner Denver®

Gardner Denver, Inc.

1800 Gardner Expressway
Quincy, IL 62305
866-440-6241

www.gardnerdenverproducts.com



©2016 Gardner Denver, Inc. Printed in U.S.A.
GSCS-VS-45-70 1st Ed. 2/16

Please recycle after use.