



COMPRESSOR DATA SHEET

Federal Uniform Test Method for Certain Air Compressors Not Applicable Rotary Compressor: Fixed Speed

MODEL DATA - FOR COMPRESSED AIR

1	Manufacturer: Gardner Denver			
2	Model Number	T55	Date:	3/3/2021
	<input checked="" type="checkbox"/> Air-cooled	<input type="checkbox"/> Water-cooled	Type:	Screw
	<input type="checkbox"/> Oil Injected	<input checked="" type="checkbox"/> Oil-Free	# of Stages:	2
3*	Rated Capacity at Full Load Operating Pressure ^{a, e}	336.0	acfm ^{a, e}	
4	Full Load Operating Pressure ^b	100	psig ^b	
5	Maximum Full Flow Operating Pressure ^c	103	psig ^c	
6	Drive Motor Nominal Rating	75	hp	
7	Drive Motor Nominal Efficiency	95.4	percent	
8	Fan Motor Nominal Rating (if applicable)	5.0	hp	
9	Fan Motor Nominal Efficiency	89.5	percent	
10*	Total Package Input Power at Zero Flow ^e	18.7	kW ^e	
11	Total Package Input Power at Rated Capacity and Full Load Operating Pressure ^d	68.9	kW ^d	
12*	Specific Package Input Power at Rated Capacity and Full Load Operating Pressure ^e	20.50	kW/100 cfm ^e	

*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator. Consult CAGI website for a list of participants in the third party verification program: www.cagi.org

NOTES:

- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex C; ACFM is actual cubic feet per minute at inlet conditions.
- b. The operating pressure at which the Capacity (Item 3) and Electrical Consumption (Item 11) were measured for this data sheet.
- c. Maximum pressure attainable at full flow, usually the unload pressure setting for load/no load control or the maximum pressure attainable before capacity control begins. May require additional power.
- d. Total package input power at other than reported operating points will vary with control strategy.
- e. Tolerance is specified in ISO 1217, Annex C, as shown in table below:

NOTE: The terms "power" and "energy" are synonymous for purposes of this document.

Volume Flow Rate at specified conditions		Volume Flow Rate	Specific Energy Consumption	No Load / Zero Flow Power
m ³ / min	ft ³ / min	%	%	%
Below 0.5	Below 17.6	+/- 7	+/- 8	+/- 10%
0.5 to 1.5	17.6 to 53	+/- 6	+/- 7	
1.5 to 15	53 to 529.7	+/- 5	+/- 6	
Above 15	Above 529.7	+/- 4	+/- 5	



Member

ROT 030.2

12/19 Rev 3

This form was developed by the Compressed Air and Gas Institute for the use of its members participating in the PVP. CAGI has not independently verified the reported data.