

# CHEMSTEEL"

## SM930 Metallic

#### **SEAL-LESS MAGNETIC DRIVE**



A full range of accessories are available including:

- line mounted pressure relief valves
- pump mounting foor for use with footless motors
- pedestal assembly

#### **GENERAL DESCRIPTION:**

Chemsteel™ pumps are designed to handle common and highly corrosive liquids that must be pumped under pressure. Manufactured to extremely precise tolerance, the Chemsteel™ pump line prevents system contamination while maintaining the purity and integrity of the liquid being pumped. Its rugged, three-section, o-ring sealed thru-bolt construction provides ease of servicing and parts replacement. Helical gearing offers noise reduction by as much as 10db, while the tandem pumps double the output flow for a single fluid, or with isolation, handle other fluids in direct ratio to the first. Additionally, Chemsteel™ pumps offer bi-directional operation for applications requiring reversing flow.

#### LIFE CYCLE/COST OF OWNERSHIP

Pump design and materials selection, together provide the longest life available from a gear pump.

Key attributes include:

- Gear & bearing combinations of metallic and nonmetallic wear surfaces.
- Slotted bearings to lubricate shaft and gear surfaces.
- Hydraulic porting to balance axial thrust and to reduce wear.
- Ample port sizing to reduce the likelihood of cavitation when inlet pressure is marginal.
- Effective housing seals with elastic memory prevent leakage of corrosives.
- · Recirculation heat port versatility.
- · Containment can flush & drain connections.

#### **SPECIFIC SOLUTIONS**


Gear/bearing design allows for "trimming" for optimizing the pump's maximum flow to reach minimum turndown or to match flow to a specific OEM's requirement.

Special materials combinations are available for specific liquids:

- Stainless or Alloy C housing construction.
- Gears available in 316 stainless, Alloy C. Also in PTFE White, Polyetheretherketone and Polyphenylenesulfide.

#### **PERFORMANCE:**

CAPACITY WATER AT 70° F / 21.1° C



Notes: For continuous service:

Plastic / Plastic gear combinations are limited to 50 psi or 3.5 bar. Metal / Plastic gear combinations are limited to 100 psi or 7 bar.

- · Shafts are 316 stainless steel or Alloy C.
- · Bearings available in carbon or PTFE White or PTFE Red.

#### FIT

Connections are 1 1/2" female NPT or BSPT, pump hardware is metric and close couple adapters mount to both NEMA and IEC standard motor frame sizes for world wide acceptance. "Near" dimensional interchangeability offers easy upgrade to Chemsteel™ pump. The port size is the same as competitive pumps.

#### **MAINTENANCE**


A three-part housing provides easy disassembly and service. Full size bearings match the gear diameter, and eliminate the need for separate wear plates. TFE encapsulating silicone o-ring pump housing seals provide elastic memory to assure an effective long lasting seal and thus avoiding the re-torquing required of pumps using pure TFE.


MODEL	SM930				
Maximum flow @1750 rpm	20 GPM	75.7 LPM			
Theoretical displacement	50.1 cc/revolution				
Maximum differential pressure	110 psig	7.6 bar			
Maximum system pressure	225 psig	15.5 bar			
Maximum speed	1800	00 RPM			
Maximum fluid temperature	450° F	232° C			
Minimum fluid temperature	-50° F	-46° C			
NPSHR @ 1750 RPM	10 feet	3.0 meters			
Standard port size	1 1/2" FNPT	1 1/2" BSPT			
Weight (lbs)	50 lbs	22.7 kg			




**DIMENSIONS** 

SM930 Metallic





SM9 MAG DRIVE W/ FOOT ACCESSORY



Mag Chemsteel Option Suffix	Power Kit Part No.	Motor Frame		*AC	D	2F	н	AE	AD	*O	*XO	*XP
M1 M	MC9H56	56C	inches	21.54	3.50	3.00	.34 Slot	13.06	5.31	6.81	2.25	7.16
			millimeters	547.1	88.9	76.2	8.6 Slot	331.7	134.9	173	57.2	181.9
M2 MC9	MCOLAST	MC9J45T 143TC/145TC	inches	24.92	3.50	4.00/5.00	0.34	13.37	5.31	6.81	2.25	7.16
	WC93431		millimeters	633	88.9	101.6/127	8.6	339.6	134.9	173	57.2	181.9
M5 MC9U	MC9U90E IEC 90SC/90LC, B14 Face	IEC 90SC/90LC,	inches	23.43	3.54	3.94/4.92	.39 Slot	12.70	5.12/4.25	6.81/6.53	n/a	5.51
		millimeters	595.1	89.9	100.1/125	9.9 Slot	322.6	130/108	173/165.9	n/a	140	
M6 MC9	MCOKOAT	MC9K84T 182TC/184TC	inches	25.00	4.50	4.50	0.41	13.48	6.38	8.75	2.25	9.09
	WC9K041	WIC9N041 1021C/1041C	millimeters	635	114.3	114.3	10.4	342.4	162.1	222.3	57.2	230.9
M7	MC9V100E	IEC 100LC, B14	inches	25.39	3.94	5.51	0.47	12.97	6.06	9.44	n/a	8.03
		Face	millimeters	644.9	100.1	140	11.9	329.4	153.9	239.8	n/a	204

<sup>\*</sup>Dimensions AC, O, XO and XP may vary depending on HP, Enclosure, Speed and Manufacturer.

To order a CHEMkit™, simply add a "K" to the end of the model number. A repair kit contains the following parts: bearings, gears, o-rings, shafts, keys, and retaining ring.



## **OBERDORFER PUMPS**

### by Gardner Denver

5900 Firestone Drive, Syracuse, NY 13206

5900 Firestone Drive, Syracuse, NY 13206 Phone: (800) 448-1668; (315) 437-0361 • Fax: (315) 463-9561 Visit **www.oberdorferpumps.com** to find in-depth descriptions of the world's leading high-quality, dependable pumps.

Due to ongoing product improvements, data shown here is subject to change without notice. Contact Oberdorfer Pumps for latest specifications.