

by Gardner Denver

Long-Reach Bottom Loading Arm



The Long-Reach Bottom Loading Arm is a long reach bottom loading arm that is ideal for extended reach bottom truck loading spots, particularly where "B-Trains" or double length trailers are being loaded. The MYR excels at long reach loading with an effective working reach ranging from 6' to 18' and a connection height envelope from 24" – 54". Not recommended where multiple arm cross-over is required.

The arm remains fully balanced with minimal effort required to easily guide the arm through its full range of motion. The arm utilizes Emco Wheaton's industry leading maintenance free D2000 swivels with multiple seal type options available. Emco Wheaton is the pioneer of this technology and the leading supplier of this configuration for the Canadian Market.



Features:

- Comes equipped with new 17-4 stainless steel compression spring.
- Overall reach up to 18ft for standard operating envelopes
- Includes D2000 sandwich design swivel joints
- Engineered with operator safety in mind
- Available in Low Temp Carbon steel for cold weather applications
- Optional API Snap-On Coupler with cold weather seals
- Features Alum D2000 Outboard Style 50 Swivel for minimal maintenance, ease of connection, and continuity of swivel sealing arrangement throughout the arm
- CRN available