

POSITIVE DISPLACEMENT BLOWERS & VACUUM PUMPS

# CycloBlower® VHX Series



## It's all about... World First Blower Technologies

**Innovation is in our DNA.** Much like DNA, the rotor design of our blowers dictate what they become. Gardner Denver has a legacy of leadership developing the world's best blowers.

### 1930's Sutorbilt Legend

- Bi-Lobe Blower Technology
- The Most Complete Offering of Air and Gas Handling Equipment in the World

### 1950's DuroFlow

- Solid Bi-Lobe Technology
- Integral Impeller-Shaft Design for Heavy-Duty Industrial Work
- Wide Operating Range = Fewer Models Needed

### 1950's CycloBlower

- WORLD'S FIRST 2×4 Helical Screw Blower
- Energy Efficiency Leader for Decades
- Patented Rotor Technology

### 1992 RBS Series

- Tri-Lobe Blower Technology
- Oversized Shafts Allowing Higher Operating Pressures and Rotation Speeds
- 100,000 Hour Bearing Lifespan

#### 2008 HeliFlow

- WORLD'S FIRST Helical Tri-Lobe Blower
- Noise Reduction Technology
- Superior Overhung Load Capacity

### 2015 CycloBlower H.E.

3×5 Fixed Helical Screw Rotor Technology

#### PATENTED ROTOR TECHNOLOGY

- Best-In-Class Energy Efficiency
- Increased Pressure Capability up to 36 psi
- Best-of-the-Best Components







The Blower Evolution continues with the **WORLD'S FIRST** variable helix technology.

CycloBlower VHX

**2018** Introducing a revolutionary variable helix rotor technology on the new CycloBlower VHX

- 3×5 Variable Helix Screw Rotor Technology
- Exclusive Blower Rotor Technology
- Game Changing Patent-Pending Design
- Premium Efficiency

The Result = the Most Extensive & Innovative Blower Line in the Industry to Meet Customer-Specific Needs

## It's all about... the Variable Helix


New revolutionary methods had to be developed to manufacture the complex variable helix rotors. This included new ideas for machining, inspection, and rotor pairing.

**—Paul Dick** Director of Operations, Americas The CycloBlower VHX utilizes a revolutionary variable helix rotor design. By adding a variable helix to our helical screw rotor design, we achieve new, unmatched levels of blower performance and efficiency.

## Why Variable Helix?

- Faster Internal Compression
- Significantly Larger Discharge Port
- Eliminates Air Losses
- Higher Efficiencies
- Efficient Turndown Capability
- Save up to 35% on your Energy Costs





### ROTOR CELL VOLUME DEVELOPMENT CYCLE

Variable vs. Fixed Helix

- Variable Helix Rotor Geometry Allows Discharge Port to Open 41° Earlier than Fixed Helix Design
- Lowering Flow Loss
- Increasing Efficiency

Highlighted Area = Port Exposure

CYCLOBLOWER VHX (VH)

FIXED HELICAL SCREW (FH)



## It's all about... Energy Savings

With energy costs continuing to rise, more efficient solutions are needed to remain competitive in the global market. The CycloBlower VHX minimizes those costs without compromising on performance.


### Make the Smart Choice & Get a Return on Your Investment

#### TOTAL COST of Blower Ownership



- Energy consumption is typically the largest cost of ownership
- Save BIG with best-in-class energy efficiency
- Lower your bottom line, increase your profits





HORSEPOWER SAVINGS


Save up to 35% on Your Energy Costs

As a company, one of our main objectives is to **increase the energy efficiency** of our products, and we continually strive to do that through innovation.

—Luke Gray Supervisor: Technology & Innovation

## It's all about... the Efficient Turndown

## Don't Lose Efficiency for Wider Turndown Capability



Turndown Efficiency Comparison

Flow (CFM)


## It's all about... the Optimized Efficiency

## Enhancing Performance Through Innovative Design

- Exclusive special cylinder designs match performance to your application requirements
- Two discharge port options optimize efficiencies based on your specific performance needs



Optimized Efficiency Modified Cylinder for Maximized Savings




Flow Standard inlet conditions are 14.7 psia, 68°F, 36% RH



## **BEST OF THE BEST**

No Corners Cut | No Compromise | Premium Parts Quality Confidence | Beyond Expectations



#### 1 O-Rings

- O-Ring Seals
- Durable Protection
- No Gaskets

#### 2 Helical Timing Gears

- Smooth, Quiet Operation at All Speeds
- Assures Non-Slip Rotor Timing

#### **3** Dual-Splash Lubrication with Eccentric Slinger Ring

- Unique Design
- Maximizes Efficiency by Reducing Power Consumption
- Optimizes Oil Distribution

#### 4 Discharge Bearings

- Axial: 4 Point Angular Contact Bearings
- Radial: Cylindrical Roller
- Provides Absolute Strength and Stability on Multiple Planes to Handle Extreme Applications
- Extended Bearing Life

To learn more about Inpro/Seal visit <u>www.inpro-seal.com</u> or scan the QR code to the right



#### 5 Inpro/Seal® Premium Oil Seal\*

- Contactless Dual-Ring Design
- Non-Wearing
- Extends Longevity Reducing Maintenance Costs
- Market-Leading Protection Against Leaks

#### 6 Piston Ring Air Seals

- Delivers Leak-Free Operation
- Provides Maximized Seal Life
- Graphite air seals for high pressure applications over 20 PSI

#### 7 Robust Ductile Iron Shaft

- Designed & Tested for Strength
- High Shaft Load Capacity
- Direct & V-Belt Drive Capable
- 8 PTFE (Polytetrafluoroethylene) Coated Rotors
  - Food Grade
  - Minimizes Air Loss
  - Maximizes Efficiency

\*Inpro/Seal is a registered trademark of Waukesha Bearings Corporation

## It's all about... Next Level Innovation

By investing in new technologies and new innovations, we are investing in our customers. We strongly believe that innovation defines our future. So, what we do today to help our customers will continue to drive our mutual success.

-Vicente Reynal, CEO, GDI





## It's all about... the Leading Edge of Technology

The CycloBlower VHX is a world first. It's really exciting as far as blower technologies go because this is as good as it gets. It's a remarkable geometry, it's a fun project that keeps Gardner Denver where it's always been, at the very bleeding edge of technology. We're always trying to do it better. We're always trying to be innovative and the VHX is a representation of that.

-Kenny Reekie, Product Director Blowers & Low Pressure

## It's all about... Made in America

Customers should be excited about the CycloBlower VHX because it's the most efficient blower in the world, backed by the Gardner Denver reputation of quality and durability. Built with pride in Sedalia, Missouri with an incredible team that's committed to quality and committed to making the best blowers in the marketplace.

-Paul Dick, Director of Operations, Americas



To learn more about the CycloBlower VHX, visit <u>www.gardnerdenver.com/en/gdproducts/</u> <u>products/blowers/helical-screw-</u> <u>technology/cycloblower-vhx</u> or scan the QR code.







## It's all about... Voice of Customer

With energy costs continuing to rise, our customers are looking for efficient solutions to minimize those costs without compromising on performance. Our latest innovation, the CycloBlower VHX incorporates a revolutionary advancement in rotor technology that addresses that energy efficiency need with a variable helix screw rotor design.

-Carl Kruthoff, Product Manager

## It's all about... Next Level Research & Development

At Gardner Denver, our products go through a rigorous research & development process. We have an extensive list of computer aided engineering tools allowing us to do a lot of the design in the virtual world rather than building multiple prototypes. Utilizing those tools to design new products like this was really put on display with this project in order to go from a very new concept to something that was production viable in a very efficient amount of time.

-Luke Gray, Supervisor: Technology & Innovation

## CycloBlower VHX Performance Data

### PRESSURE

MODEL	SPEED RPM	5 PSIG		8 PSIG		11 PSIG		14 PSIG		17 PSIG		20 PSIG	
		CFM	BHP	CFM	BHP	CFM	BHP	CFM	BHP	CFM	BHP	CFM	BHP
100CDL300 RC1	1200 1860 2520 3180 3840 4500	144.3 267.3 390.8 514.8 639.3 764.3	4.9 7.8 11.1 14.8 18.9 23.4	122.9 246.0 369.7 493.9 618.5 743.7	7.1 11.1 15.5 20.3 25.5 31.1	102.7 226.0 349.9 474.2 599.1 724.4	9.5 14.6 20.1 26.1 32.4 39.1	83.8 207.3 331.3 455.9 580.9 706.4	12.3 18.5 25.1 32.1 39.6 47.4	- 189.9 314.1 438.8 564.0 689.7	22.7 30.4 38.5 47.1 56.0	- - - - -	- - - -
100CDL300 RC2	1200 1860 2520 3180 3840 4500	144.4 263.2 383.3 504.6 627.3 751.3	5.5 9.5 13.8 18.5 23.6 29.1	128.9 248.3 369.0 490.9 614.2 738.8	7.3 12.1 17.2 22.7 28.6 34.8	114.4 234.4 355.6 478.1 601.9 727.1	9.3 14.8 20.8 27.0 33.7 40.7	100.8 221.3 343.1 466.2 590.6 716.3	11.5 17.8 24.5 31.6 39.0 46.9	88.0 209.1 331.4 455.1 580.1 706.3	13.9 21.0 28.5 36.3 44.6 53.2	- 320.7 444.9 570.5 697.3	- 32.6 41.3 50.3 59.7

### VACUUM

MODEL	SPEED RPM	5 IN. HG.		8 IN. HG.		11 IN. HG.		14 IN. HG.		17 IN. HG.		18 IN. HG.	
		CFM	BHP	CFM	BHP	CFM	BHP	CFM	BHP	CFM	BHP	CFM	BHP
100CDL300 RC1	1200 1860 2520	162.1 282.9 404.9	2.7 4.7 7.0	148.2 269.2 391.4	4.1 6.3 8.9	131.5 252.7 375.1	5.7 8.2 10.9	111.4 232.9 355.6	7.2 10.0 13.1	-	-	-	-
	3180 3840 4500	528.1 652.4 777.9	9.7 12.6 15.8	514.7 639.3 765.0	11.7 14.8 18.2	498.7 623.5 749.4	14.0 17.3 21.0	479.5 604.6 730.9	16.5 20.2 24.2	- -	- -	- -	- -
100CDL300 RC2	1200 1860 2520 3180 3840 4500	152.0 272.5 393.3 514.4 635.7 757.4	3.2 6.4 9.8 13.4 17.3 21.4	144.7 265.6 386.7 508.2 629.9 751.8	3.9 7.1 10.6 14.2 18.1 22.2	135.4 256.8 378.4 500.4 622.6 745.0	4.8 8.0 11.5 15.2 19.1 23.3	123.5 245.5 367.9 490.4 613.3 736.4	5.8 9.1 12.6 16.4 20.4 24.6	107.7 230.8 354.0 477.6 601.4 725.5	6.9 10.3 13.9 17.7 21.8 26.1	101.4 224.8 348.5 472.5 596.8 721.3	7.2 10.6 14.3 18.2 22.3 26.6





## CycloBlower VHX Dimensions


## MODEL 100CDL300


DIMENSIONS*	INCHES	MM
А	7.283	185.00
В	4.311	109.50
С	29.130	739.90
D	6.890	175.00
E	6.890	175.00
F	5.945	151.00
G	15.827	402.00
Н	14.173	360.00
J	1.889	48.00
K	0.354 × 0.551 × 3.937	9.00 × 14.00 × 100.00
L	13.535	343.80
Μ	6.890	175.00
Ν	6.000 ANSI 125 FF	150.00 ISO 7005 ( PN10 )
Q	5.811	127.60
S	13.780	350.00
Т	6.890	175.00
U	4.921	125.00
V	6.646	168.80
W	5.000 ANSI 125 FF	125.00 ISO 7005 ( PN10 )
Х	0.689	17.50
Z	22.118	561.80

\*Dimensions are for a bottom-discharge unit.









## The leader in every market we serve by continuously improving all business processes with a focus on innovation and velocity



#### Gardner Denver, Inc.

1800 Gardner Expressway Quincy, IL 62305 866-428-4890 www.gardnerdenver.com/gdproducts

©2018 Gardner Denver, Inc. Printed in U.S.A. PD-CB-VHX 3rd Ed. 10/18





